

MODL.VARIO Accessories closure plug 8/6

for adaptive inserts, nickel plated brass

Modlink Vario

Accessories

Locking plug

Diameter

8 mm

Quantity: 10 pcs.

good resistance to oil, gasoline and chemicals

The resistance to aggressive media should be individually tested for your application. Further details on request.

[Link do produto](#)**Ilustração**

Produto pode diferir da imagem

Dados comerciais

| | |
|--------------------------|---------------|
| ECLASS-6.0 | 27260702 |
| ECLASS-6.1 | 27269202 |
| ECLASS-7.0 | 27449203 |
| ECLASS-8.0 | 27449203 |
| ECLASS-9.0 | 27440192 |
| ECLASS-10.1 | 27440192 |
| ECLASS-11.1 | 27440192 |
| ECLASS-12.0 | 27440192 |
| ETIM-5.0 | EC002641 |
| Classificação fiscal | 85389099 |
| GTIN | 4048879618892 |
| Quantidade por embalagem | 10 |

Mechanical data

| | |
|-------------------------|----------|
| Operating pressure min. | -0,8 bar |
| Operating pressure max. | 16 bar |

Mechanical data | Material data

| | |
|------------------|---------------|
| Coating housing | nickel plated |
| Material housing | Brass |

Mechanical data | Mounting data

| | |
|--------|-------|
| Size | AD8 |
| Height | 19 mm |

| | |
|-------|-------|
| Width | 10 mm |
| Depth | 10 mm |

Environmental characteristics | Climatic

| | |
|----------------------------|--------|
| Operating temperature min. | -20 °C |
| Operating temperature max. | 120 °C |