




MEF EMC-FILTER 3-PHASE 2-STAGE

I:12A U:3x500 VAC book-style

: 12 A
2-stage



	max. 3 x 500 V AC
	50...60 Hz
	18 x (IN t) max. 0.5 ms; 1.5 x (IN t) max. 1 min. (1 x per hour)
	max. 15 mA (250 V AC)
	0.2...10 mm ² (AWG 24...7); 0.2...6 mm ² (AWG 24...9)
()	3.3 kV (L-N), 2 s; 3.1 kV (L-L), 2 s
	;
HxWxD	226x50x140 mm
	25/085/21 (EN 60068-1)
	3 1stage (MEF 3/1) & 3 2 stage (MEF 3/2) 0.1...30MHz , . TN-C main . .(100mm). EMC . SMPS ,
EAN	4048879029162
eClass	27130806
	85363010
	IT
	1