



MASI20 INSTALLATION TECHNOLOGY

Distributor 2x AS-I and 3x extern power

2 AS-Interface + 3 power ports
potentially separated
5 plug terminals included

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료	
ECLASS-6.0	27279219
ECLASS-6.1	27279219
ECLASS-7.0	27279219
ECLASS-8.0	27279219
ECLASS-9.0	27440108
ECLASS-10.1	27440111

ECLASS-11.1	27440111
ECLASS-12.0	27440111
ETIM-5.0	EC001596
GTIN	4048879050593
세번부호	85176200
포장단위	1
Electrical data Supply	
Operating voltage DC max.	36 V
Current operating per port max.	8 A
Total current max.	24 A
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Insulation strength ASI/Power	200 V
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	52 mm
Width	67 mm
Depth	90 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	70 °C
Storage temperature min.	-40 °C
Storage temperature max.	80 °C
Conformity	
Product standard	EN 60664-1
Connection type 5	
Connection type 1	Asi Bus
Connection type 2	Power 1
Connection type 3	Power 2
Connection type 4	Power 3
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	A +
PIN 2	A -
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	1 +
PIN 2	1 -
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	2 +

PIN 2	2 -
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	3 +
PIN 2	3 -
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	8
PIN 1	A +
PIN 2	A -
PIN 3	1 +
PIN 4	1 -
PIN 5	2 +
PIN 6	2 -
PIN 7	3 +
PIN 8	3 -