

8 Port unmanaged Gigabit Switch 8 PoE Ports IP20 metal

8 Port Unmanaged IP20 PoE Gigabit Switch
24 V power supply
8 PoE ports

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료	
ECLASS-6.1	19170106
ECLASS-7.0	19170106
ECLASS-8.0	19170106
ECLASS-9.0	19170402
ECLASS-10.1	19170402
ECLASS-11.1	19170402
ECLASS-12.0	19170402
GTIN	4048879844208
세번부호	85176200
포장단위	1
Electrical data Supply	
Operating voltage DC min.	12 V
Operating voltage DC max.	57 V
PoE voltage amplifier	yes
Industrial communication	
Data transmission rate max.	1000 MBit/s
Industrial communication Ethernet functionality	
Auto-crossover	yes
Auto-negotiation	yes
duplex	Full duplex
Switch type	unmanaged
VLAN unmanaged (IEEE 802.1Q)	no

Diagnostics

Alarm contact	yes
Diagnostic	No voltage
LED display	Ethernet connection/data traffic

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

Mechanical data | Material data

Color housing	black
Material housing	Metal

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)
Height	145 mm
Width	57,8 mm
Depth	113 mm

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	70 °C
Storage temperature min.	-40 °C
Storage temperature max.	85 °C

Connection type 2

Connection type 1	8
Connection type 2	X1
Family construction form	RJ45
Gender	female
Color contact carrier	black
No. of poles	8
PIN 1	TD +
PIN 2	TD -
PIN 3	RD +
PIN 4	n.c.
PIN 5	n.c.
PIN 6	RD -
PIN 7	n.c.
PIN 8	n.c.
Connection	Plug-in terminals RK
Family construction form	terminal
Gender	male
Color contact carrier	green
No. of poles	7
PIN 1	FE
PIN 2	V 1 -
PIN 3	V 1 +
PIN 4	Relay (NO)
PIN 5	Relay (NO)
PIN 6	V 2 -
PIN 7	V 2 +