




Emergency stop with 2 positive opening

contacts in a 42mm enclosure

E-Stop 42 2NC M12(5)
with M12 connection
5-pole
Emergency-Stop button
2 NC (positively-opening)
mounting with clip on the back side

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료	
ECLASS-6.0	27371244
ECLASS-6.1	27371244
ECLASS-7.0	27371244
ECLASS-8.0	27371244

ECLASS-9.0	27371244
ECLASS-10.1	27371244
ECLASS-11.1	27371244
ECLASS-12.0	27371244
ETIM-5.0	EC002034
GTIN	4048879594202
세번부호	85365080
포장단위	1
Electrical data Supply	
Operating voltage AC	24 V
Operating voltage DC	24 V
Operating current	2 A
Device protection	
Condition lifetime	load-dependent, temperature dependent
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65
Electrical lifetime	50000 Cycles
Device protection Mechanical	
Mechanical endurance	50000 Cycles
Operating life B10d	250000 Cycles
Mechanical data	
Bounce time max.	10 ms
Mechanical data Material data	
Material contact	AgNi
Mechanical data Mounting data	
Height	52 mm
Width	124 mm
Depth	42 mm
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	70 °C
Storage temperature min.	-25 °C
Storage temperature max.	85 °C
Technical Data Reliability	
Lambda normally closed contact	20 %
Connection type 1	
Family construction form	M12
Gender	male
Color contact carrier	black
Coding	A
No. of poles	5
PIN 1	NC 2
PIN 2	NC 1 +
PIN 4	NC 2 +
PIN 5	NC 2