

LED-INDICATOR OPAC / GREEN

LED-230VAC IP65

(green)
230 V AC
The modules are suitable for wall thickness of 1.5...5.0 mm.

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료

ECLASS-6.0	27261590
ECLASS-6.1	27261501
ECLASS-7.0	27261501
ECLASS-8.0	27261501
ECLASS-9.0	27261501
ECLASS-10.1	27261501
ECLASS-11.1	27261501
ECLASS-12.0	27261501
ETIM-5.0	EC000272
GTIN	4048879041256
세번부호	85318070
포장단위	10

Electrical data | Supply

Operating voltage AC	230 V
Operating voltage AC min.	207 V
Operating voltage AC max.	253 V
Current consumption min.	8 mA
Current consumption max.	12 mA

Installation | Connection

Connection information Faston 2.8×0.8 mm

Device protection | Electrical

Degree of protection (EN IEC 60529) IP65

Device protection | Media

Flame resistance flame retardant

Mechanical data

Diameter LED 5 mm

Mechanical data | Material data

Material housing Plastic

Mechanical data | Mounting data

Diameter front panel drilling 9 mm

Environmental characteristics | Climatic

Operating temperature min. -20 °C

Operating temperature max. 50 °C