

LED-INDICATOR GREEN

LED 5mm - 24V AC/DC - 15mA - IP67

(green)
24 V AC/DC
Protection IP67

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.

제품자료	
ECLASS-6.0	27261590
ECLASS-6.1	27261501
ECLASS-7.0	27261501
ECLASS-8.0	27261501
ECLASS-9.0	27261501
ECLASS-10.1	27261501
ECLASS-11.1	27261501
ECLASS-12.0	27261501
ETIM-5.0	EC000272
GTIN	4048879040716
세번부호	85318070

포장단위	10
Electrical data Supply	
Operating voltage AC	24 V
Operating voltage AC min.	20,4 V
Operating voltage AC max.	26,4 V
Operating voltage DC	24 V
Operating voltage DC min.	20,4 V
Operating voltage DC max.	26,4 V
Current consumption min.	13 mA
Current consumption max.	17 mA
Installation Connection	
Connection information	Faston 2.8x0.8 mm
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP67
Mechanical data	
Diameter LED	5 mm
Mechanical data Material data	
Color housing	gray
Material housing	PVC
Mechanical data Mounting data	
Diameter front panel drilling	8 mm
Height	18,5 mm
Width	12 mm
Depth	53 mm
Environmental characteristics Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	70 °C