


ECO-RAIL-2 POWER SUPPLY 1-PHASE,
IN: 90 ... 132 VAC / 173 ... 264 VAC OUT: 24V/20ADC

INPUT: 90...132 V AC/173...264 V AC
OUTPUT: 23...28 V DC
Current: 20 A
Mains failure bridging min.
min. 15 ms (115 V AC); min. 20 ms (230 V AC)

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료	
ECLASS-6.0	27049002
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-8.0	27049002
ECLASS-9.0	27040701
ECLASS-10.1	27040701
ECLASS-11.1	27040701
ECLASS-12.0	27040701
ETIM-5.0	EC002540
GTIN	4048879694636
세번부호	85044083
포장단위	1
Electrical data	
Number of devices series connection max.	2
Parallel connection	no
Series connection	yes
Electrical data Supply	
Power frequency	50 ... 60 Hz
Electrical data Input	

Fuse protection primary side internal	12 A
Characteristic back-up fuse	Inertia
Input voltage 1 AC	100 V
Input voltage 1 AC min.	90 V
Input voltage 1 AC max.	132 V
Input voltage 2 AC	200 V
Input voltage 2 AC min.	173 V
Input voltage 2 AC max.	264 V
Input current at input voltage 1 AC	7,8 A
Input current at input voltage 2 AC	4 A
Inrush current max.	40 A @ 230 V
Efficiency	89 % @ 115 V AC, 90 % @ 230 V AC

Electrical data | Output

Output voltage DC	24 V
Output voltage DC min.	23 V
Output voltage DC max.	28 V
Output voltage adjustable	yes
Output current	20 A
Ripple effective max.	50 mV
Spikes (s-s) max.	100 mV

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
Overload protection output	yes
Short-circuit protection output	yes

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)
Height	124 mm
Width	105 mm
Depth	124 mm

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	40 °C
Derating from	40 °C
Storage temperature min.	-20 °C
Storage temperature max.	85 °C
Relative humidity min. (operation)	20 %
Relative humidity max. (operation)	90 % no condensation

Connection type 2

Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	3
PIN 1	PE
PIN 2	N
PIN 3	L
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green

No. of poles	4
PIN 1	-
PIN 2	-
PIN 3	+
PIN 4	+