

MCS-A ASI POWER SUPPLY 1-PHASE,

IN: 95-265VAC OUT: 30,5V/4ADC

INPUT: 95...265 V AC

Current: 4 A

Single-phase, primary switched

Protection IP20



Mains failure bridging min.

min. 14 ms (110 V AC); min. 80 ms (230 V AC)

Unit complies to AS-Interface specification for power supplies (PELV)

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료

ECLASS-6.0	27049002
ECLASS-6.1	27049002
ECLASS-7.0	27049002

ECLASS-8.0	27049002
ECLASS-9.0	27040701
ECLASS-10.1	27040701
ECLASS-11.1	27040701
ECLASS-12.0	27040701
ETIM-5.0	EC002540
GTIN	4048879079907
세번부호	85044083
포장단위	1

Electrical data | Supply

Power frequency	50 ... 60 Hz
-----------------	--------------

Electrical data | Input

Characteristic back-up fuse	Inertia
Input voltage AC min.	95 V
Input voltage AC max.	265 V
Current input AC	2,1 A
Inrush current max.	35 A @ 230 V
External back-up fuse per phase max.	10 A
Efficiency	83 % @ 110 V AC, 85 % @ 230 V AC

Electrical data | Output

Output suppression	Filter acc. to AS-Interface specification
Output voltage DC	30,5 V
Output voltage DC min.	29,89 V
Output voltage DC max.	31,11 V
Output voltage adjustable	no
Output current max.	4 A
Ripple effective max.	20 mV
Power rating DC max.	122 W

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
Overload protection output	yes
Short-circuit protection output	yes

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)
Height	115 mm
Width	54 mm
Depth	147 mm

Environmental characteristics | Climatic

Operating temperature min.	-10 °C
Operating temperature max.	55 °C
Derating from	40 °C
Storage temperature min.	-25 °C
Storage temperature max.	85 °C

Conformity

Product standard	IEC 61010-2-201
EMC	EN 55022 B
Low Voltage Directive	EN 61204-3

Connection type 2

Connection	Spring clamp terminals FK
Family construction form	terminal

Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	+
PIN 2	-
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	3
PIN 1	PE
PIN 2	N
PIN 3	L