

FREQUENCY/VOLTAGE-CURRENT-CONVERTER



IN: 0..100 kHz - OUT: 0..10 V / (0)4..20 mA

INPUT: 0...1, 0...10, 0...100 kHz
OUTPUT: 0...10 V DC, 0...20 mA, 4...20 mA
Spring clamp terminals
Input and output galvanically separated

The new frequency converter in the slim MIRO housing can be universally used. The frequency that is applied on the three inputs, will be galvanically isolated, transformed and is available as analog signal on all three outputs.

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료	
ECLASS-6.0	27210990
ECLASS-6.1	27210904
ECLASS-7.0	27210904
ECLASS-8.0	27210904

ECLASS-9.0	27210904
ECLASS-10.1	27210904
ECLASS-11.1	27210904
ECLASS-12.0	27210904
ETIM-5.0	EC002653
GTIN	4048879022392
세번부호	85437090
포장단위	1

Electrical data

Settling time max.	350 ms
Accuracy (of full scale)	0,5 %

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	19,2 V
Operating voltage DC max.	28,8 V
Operating current max.	80 mA

Electrical data | Input

Input current min.	6 mA
Input current max.	25 mA
Input resistor	1,2 kΩ

Electrical data | Output

Output voltage DC min.	0 V
Output voltage DC max.	10 V

Device protection | Electrical

Rated surge voltage	2,5 kV
---------------------	--------

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	mounting rail, (EN 60715)
Height	92 mm
Width	12,4 mm
Depth	70 mm

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	50 °C

Connection type 5

Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	+ 24 V DC
PIN 2	GD
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	I 2
PIN 2	GD
Connection	Spring clamp terminals FK
Family construction form	terminal

이 데이터 시트에 포함된 정보는 최대한의 주의로 작성되었습니다.
2024-05-10

Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	U
PIN 2	I 1
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	f 3
PIN 2	GD 1
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	f 1
PIN 2	f 2