


MIRO 6.2 pluggable compl. Module Optocoupler

IN: 24 VDC - OUT: 24 VDC / 6 A

Transistor 6 A
24 V DC
Spring clamp terminals
Complete module

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료	
ECLASS-6.0	27371604
ECLASS-6.1	27371604
ECLASS-7.0	27371604
ECLASS-8.0	27371604
ECLASS-9.0	27371604
ECLASS-10.1	27371604

ECLASS-11.1	27371604
ECLASS-12.0	27371604
ETIM-5.0	EC001504
GTIN	4048879532747
세번부호	85365005
포장단위	1
Electrical data Input	
Input voltage DC	24 V
Input voltage DC min.	18 V
Input voltage DC max.	30 V
Input current	9 mA
Electrical data Output	
Switch off delay max.	31 µs
Forward voltage max.	240 mV
Switching frequency inductive max.	50 Hz
Switching frequency ohmic max.	500 Hz
Voltage switching DC min.	3 V
Switching voltage DC max.	30 V
Switching current min.	10 mA
Switching current max.	6 A
Diagnostics	
Status indication LED	yellow
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP20
Rated insulation voltage	50 V
Rated surge voltage	2,5 kV
Mechanical data Mounting data	
Mounting method	inserted
Height	93 mm
Width	6,2 mm
Depth	75,6 mm
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	50 °C