

MODLINK MSDD SOCKET INSERT GERMANY

250VAC/16A with LED yellow

Germany (VDE) white
Screw terminals
LED (yellow)

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료

ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
GTIN	4048879038294
세번부호	85366990
포장단위	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	68 mm

Environmental characteristics | Climatic

Storage temperature min.	-30 °C
Storage temperature max.	60 °C

Germany (VDE)

Connection cross section max.	6 mm²
-------------------------------	-------

AWG number max.	10
Operating voltage AC	250 V
Operating current	16 A
Status indication LED	yellow
Connection	Screw terminals SK
No. of poles	2 + PE
Connections per pole	2
Protection contact present	yes