

MODLINK MSDD SOCKET INSERT USA NEMA 5-15

125VAC/15A soldering connection

USA (NEMA 5-15)  
Plug-solder connection  
125 V AC

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



| 제품자료                                     |               |
|------------------------------------------|---------------|
| ECLASS-6.0                               | 27189217      |
| ECLASS-6.1                               | 27189217      |
| ECLASS-7.0                               | 27189217      |
| ECLASS-8.0                               | 27189217      |
| ECLASS-9.0                               | 27182806      |
| ECLASS-10.1                              | 27182806      |
| ECLASS-11.1                              | 27182806      |
| ECLASS-12.0                              | 27182806      |
| ETIM-5.0                                 | EC000020      |
| GTIN                                     | 4048879038270 |
| 세번부호                                     | 85366990      |
| 포장단위                                     | 1             |
| Mechanical data   Mounting data          |               |
| Height                                   | 88 mm         |
| Width                                    | 51 mm         |
| Depth                                    | 30 mm         |
| Environmental characteristics   Climatic |               |
| Storage temperature min.                 | 5 °C          |
| Storage temperature max.                 | 40 °C         |
| USA                                      |               |
| Connection geometry                      | 4.8 x 0.5 mm  |

|                            |                        |
|----------------------------|------------------------|
| Operating voltage AC       | 125 V                  |
| Operating current          | 15 A                   |
| Connection                 | Plug-solder connection |
| No. of poles               | 2 + PE                 |
| Protection contact present | yes                    |