

MODLINK MSDD SOCKET INSERT USA NEMA 5-15

125VAC/3A with fuse

USA (NEMA 5-15)
with fuse
Plug-solder connection

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료	
ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
GTIN	4048879038195
세번부호	85366990
포장단위	1
Mechanical data Mounting data	
Height	88 mm
Width	51 mm
Depth	60 mm
Environmental characteristics Climatic	
Storage temperature min.	10 °C
Storage temperature max.	60 °C
Fuse	
Operating voltage AC	250 V

Operating voltage DC	32 V
Nominal current	3 A
USA	
Connection geometry	4.8 x 0.5 mm
Operating voltage AC	125 V
Operating current	3 A
Connection	Plug-solder connection
No. of poles	2 + PE
Protection contact present	yes