

MODLINK MSDD CABLE ENTRY SYSTEM

KDP/R

round (M50)
For sale only in packing units
Cable diameter (3)× 6...10 mm, (1)× 9.6...15.9 mm

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.

제품자료	
ECLASS-6.0	27189217
ECLASS-6.1	27400604
ECLASS-7.0	27400604
ECLASS-8.0	27400604
ECLASS-9.0	27400604
ECLASS-10.1	27400604
ECLASS-11.1	27400604
ECLASS-12.0	27400604
ETIM-5.0	EC000211
GTIN	4048879031639
세번부호	39269097
포장단위	1
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65
Mechanical data Material data	
Material housing	PA
Mechanical data Mounting data	
Mounting method	screwed, geschnappt
Sheet thickness min. (snap-on mounting)	1,5 mm
Sheet thickness max. (snap-on mounting)	2 mm
Sheet thickness min. (screw mounting)	1,5 mm
Sheet thickness max. (screw mounting)	2 mm
Height	33 mm
Width	58 mm
Depth	58 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	70 °C