

COMLIGHT57 LED RED STATUS LIGHT

Product discontinued

Compact status light
Flange M12 male, 4-pole
red

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료	
ECLASS-6.0	27371220
ECLASS-7.0	27371220
ECLASS-8.0	27371220
ECLASS-9.0	27371220
ETIM-5.0	EC000232
GTIN	4048879439176
세번부호	85318070
포장단위	1
Electrical data Supply	
Operating voltage DC	24 V
Current consumption max.	25,9 mA
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked
Mechanical data Material data	
Material housing	Plastic
Mechanical data Mounting data	
Height	78,4 mm
Width	57 mm
Depth	57 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	50 °C

Connection type 1

Family construction form	M12
Gender	male
Coding	A
No. of poles	4
PIN 3	BU 0 V
PIN 4	BK 24 V DC