

MODLIGHT70 LED FLASH MODUL AMBER

Product discontinued, no alternative

제품 링크

| 제품자료                                     |                  |
|------------------------------------------|------------------|
| ECLASS-6.0                               | 27371220         |
| ECLASS-7.0                               | 27371220         |
| ECLASS-8.0                               | 27371220         |
| ECLASS-9.0                               | 27371220         |
| ETIM-5.0                                 | EC000232         |
| GTIN                                     | 4048879030991    |
| 세번부호                                     | 85319000         |
| 포장단위                                     | 1                |
| Electrical data   Supply                 |                  |
| Operating voltage DC                     | 24 V             |
| Operating voltage DC min.                | 21,6 V           |
| Operating voltage DC max.                | 26,4 V           |
| Current consumption min.                 | 250 mA           |
| Current consumption max.                 | 430 mA           |
| Device protection   Electrical           |                  |
| Degree of protection (EN IEC 60529)      | IP65             |
| Additional condition protection degree   | inserted, locked |
| Mechanical data   Material data          |                  |
| Material housing                         | PC               |
| Mechanical data   Mounting data          |                  |
| Height                                   | 49 mm            |
| Width                                    | 70 mm            |
| Depth                                    | 70 mm            |
| Environmental characteristics   Climatic |                  |
| Operating temperature min.               | -10 °C           |
| Operating temperature max.               | 60 °C            |