

SIGNAL TOWER MODLIGHT30 EQUIPPED WITH LED MODULES

Green,amber,red with 4 pole M12 connection

Connection module + LED modules
green, yellow, red
with M12 connection
Connection cables are in the online shop under "Connection Technology".

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료	
ECLASS-6.0	27371230
ECLASS-6.1	27371230
ECLASS-7.0	27371230
ECLASS-8.0	27371230
ECLASS-9.0	27371230
ECLASS-10.1	27371230
ECLASS-11.1	27371230
ECLASS-12.0	27371230
ETIM-5.0	EC001042
GTIN	4048879496896
세번부호	85318070
포장단위	1
Electrical data Supply	
Operating voltage AC	24 V
Operating voltage DC	24 V
Current consumption max.	85 mA
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65
Mechanical data Material data	
Color housing	black

Material housing	Plastic
Mechanical data Mounting data	
Height	30 mm
Width	30 mm
Depth	213 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Connection type 1	
Family construction form	M12
Gender	male
Coding	A
No. of poles	4
PIN 1	GN
PIN 2	RD
PIN 3	COM
PIN 4	YE