

Modlight50 Pro connecting modul base mounting

Input 24VDC

Base for floor mount  
Connection cables are in the online shop under "Connection Technology".

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료

|             |               |
|-------------|---------------|
| ECLASS-6.0  | 27371232      |
| ECLASS-6.1  | 27371232      |
| ECLASS-7.0  | 27371232      |
| ECLASS-8.0  | 27371232      |
| ECLASS-9.0  | 27371232      |
| ECLASS-10.1 | 27371232      |
| ECLASS-11.1 | 27371232      |
| ECLASS-12.0 | 27371232      |
| ETIM-5.0    | EC001152      |
| ETIM-6.0    | EC001152      |
| ETIM-7.0    | EC001152      |
| GTIN        | 4048879751551 |
| 세번부호        | 85319000      |
| 포장단위        | 1             |

Electrical data | Supply

|                           |        |
|---------------------------|--------|
| Operating voltage DC      | 24 V   |
| Operating voltage DC min. | 21,6 V |
| Operating voltage DC max. | 26,4 V |

Device protection | Electrical

|                                        |                  |
|----------------------------------------|------------------|
| Degree of protection (EN IEC 60529)    | IP65             |
| Additional condition protection degree | inserted, locked |

Mechanical data | Material data

|                                          |                           |
|------------------------------------------|---------------------------|
| Color housing                            | black                     |
| Material housing                         | Plastic                   |
| Mechanical data   Mounting data          |                           |
| Height                                   | 180 mm                    |
| Width                                    | 50 mm                     |
| Depth                                    | 50 mm                     |
| Environmental characteristics   Climatic |                           |
| Operating temperature min.               | -30 °C                    |
| Operating temperature max.               | 60 °C                     |
| Connection type 1                        |                           |
| Connection                               | Spring clamp terminals FK |
| Family construction form                 | terminal                  |
| Gender                                   | female                    |
| No. of poles                             | 9                         |
| PIN 1                                    | LED-Modul RD              |
| PIN 2                                    | LED-Modul YE              |
| PIN 3                                    | LED-Modul GN              |
| PIN 4                                    | LED-Modul BU              |
| PIN 5                                    | LED-Modul CL              |
| PIN 6                                    | Buzzer                    |
| PIN 7                                    | 24 V DC (0 V)             |
| PIN 8                                    | Blinking                  |
| PIN 9                                    | 0 V (24 V DC)             |