

Modlight50 Pro connecting modul tube mounting

Input 24VDC

Basic for tube mounting
Connection cables are in the online shop under "Connection Technology".

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료

ECLASS-6.0	27371232
ECLASS-6.1	27371232
ECLASS-7.0	27371232
ECLASS-8.0	27371232
ECLASS-9.0	27371232
ECLASS-10.1	27371232
ECLASS-11.1	27371232
ECLASS-12.0	27371232
ETIM-5.0	EC001152
ETIM-6.0	EC001152
ETIM-7.0	EC001152
GTIN	4048879751513
세번부호	85319000
포장단위	1

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	26,4 V

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked

Mechanical data | Material data

Color housing	black
Material housing	Plastic
Mechanical data Mounting data	
Height	180 mm
Width	50 mm
Depth	50 mm
Environmental characteristics Climatic	
Operating temperature min.	-30 °C
Operating temperature max.	60 °C
Connection type 1	
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
No. of poles	9
PIN 1	LED-Modul RD
PIN 2	LED-Modul YE
PIN 3	LED-Modul GN
PIN 4	LED-Modul BU
PIN 5	LED-Modul CL
PIN 6	Buzzer
PIN 7	24 V DC (0 V)
PIN 8	Blinking
PIN 9	0 V (24 V DC)