

COMLIGHT56 LED STATUS LIGHT

Multicolor, touch sensor, IO-Link

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료

|             |               |
|-------------|---------------|
| ECLASS-6.0  | 27371220      |
| ECLASS-6.1  | 27110390      |
| ECLASS-7.0  | 27110390      |
| ECLASS-8.0  | 27110390      |
| ECLASS-9.0  | 27110350      |
| ECLASS-10.1 | 27110350      |
| ECLASS-11.1 | 27110350      |
| ECLASS-12.0 | 27110350      |
| ETIM-5.0    | EC000232      |
| GTIN        | 4048879868457 |
| 세번부호        | 85319000      |
| 포장단위        | 1             |

Electrical data | Supply

|                           |       |
|---------------------------|-------|
| Operating voltage DC      | 24 V  |
| Operating voltage DC min. | 18 V  |
| Operating voltage DC max. | 30 V  |
| Nominal current           | 40 mA |
| Nominal rating            | 1 W   |

Industrial communication | IO-Link

|                                    |         |
|------------------------------------|---------|
| IO-Link process data length output | 1 Bytes |
| IO-Link process data length input  | 2 Bytes |
| IO-Link revision ID                | V1.1    |
| IO-Link type                       | Device  |

이 데이터 사이트에 포함된 정보는 최대한의 주의로 작성되었습니다.  
2024-05-07

|                                          |                        |
|------------------------------------------|------------------------|
| IO-Link cycle time min.                  | 8 ms                   |
| IO-Link transmission rate                | COM2 (38.4 kbit/s)     |
| Port Class                               | A                      |
| Device protection   Electrical           |                        |
| Degree of protection (EN IEC 60529)      | IP65                   |
| Additional condition protection degree   | inserted, locked       |
| Mechanical data                          |                        |
| Input method touch sensor                | Electrostatic capacity |
| Mechanical data   Material data          |                        |
| Material housing                         | PC                     |
| Mechanical data   Mounting data          |                        |
| Height                                   | 97,2 mm                |
| Width                                    | 56 mm                  |
| Depth                                    | 56 mm                  |
| Environmental characteristics   Climatic |                        |
| Operating temperature min.               | -25 °C                 |
| Operating temperature max.               | 60 °C                  |
| Storage temperature min.                 | -40 °C                 |
| Storage temperature max.                 | 75 °C                  |
| Connection type 1                        |                        |
| Family construction form                 | M12                    |
| Gender                                   | male                   |
| Coding                                   | A                      |
| No. of poles                             | 4                      |
| PIN 1                                    | BN 24 V DC (0 V)       |
| PIN 3                                    | BU 0 V (24 V DC)       |
| PIN 4                                    | BK IO-Link             |