

Modlight70 Pro buzzer

4 tones

Buzzer modules

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



제품자료

ECLASS-6.0	27371200
ECLASS-6.1	27371237
ECLASS-7.0	27371237
ECLASS-8.0	27371237
ECLASS-9.0	27371237
ECLASS-10.1	27371237
ECLASS-11.1	27371237
ECLASS-12.0	27371237
ETIM-5.0	EC001152
GTIN	4048879752497
세번부호	85318070
포장단위	1

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	26,4 V
Current consumption max.	62,5 mA

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked

Mechanical data | Material data

Material housing	PC
------------------	----

Mechanical data | Mounting data

Height	49 mm
Width	70 mm
Depth	70 mm
Environmental characteristics Climatic	
Operating temperature min.	-30 °C
Operating temperature max.	60 °C
Connection type 1	
Mounting method	bayonet-locking