





**M12 MALE 0° / M12 FEMALE 0° LED**



PUR 4X0.34 GRAY, UL/CSA, drag ch 1m


Male – female  
 M12 – M12, 4  
 2× LED (PNP), (NPN - )  
 Art-No. 7005 -M12 Lite ( , )



Male

Female





\* UL/CSA

	40311
/	4 × 0.34 mm <sup>2</sup>
	PP ( , , )
C-track	10 Mio.
	PUR (UL/CSA)
	4.5 mm ±5%
( )	10 × Ø
( )	-40...+80 °C
( )	-25...+80 °C
	234
	3 (PUR)
( )	cRUus (AWM-Style 20549/10493); CE conform
[G/m]	36,30
(wire)	,
( )	max. 57 Ω/km (20 °C)
-Ø	0.1 mm
( )	42 × 0.1 mm (6 )
( )	4 × 0.34 mm <sup>2</sup>
AWG	AWG 22
( )	PP
( )	CFC, , , ,
( )	70 ±5 D
-Ø	1.25 mm ±5%
/	, , ,
	4
(shielded)	no
	PUR
( )	CFC, , , , , , , , , ,
( )	90 ±5 A
-Ø ( )	4.5 mm ±5%
( )	, , (EN 60811-404)
	300 V AC
	2500 V AC
	DIN VDE 0298-4
( )	-40...+80 °C, (+90 °C 10 000 )
( )	-25...+80 °C, (+90 °C 10 000 )
( )	5 × Ø
( )	10 × Ø
(C-track)	max. 10 Mio. (25 °C)
(C-track)	max. 3 m/s
(C-track)	max. 10 m/s <sup>2</sup>
	±180°/m
	max. 2 Mio. (25 °C)

35

	24 V DC $\pm 25\%$
(UL )	max. 30 V DC
	max. 4 A
	0.8 kV
	IEC 60664-1, category I
	A-coded
LED	/
	(M12×1 mm) 0.6 Nm ,
	M12 (SW13)
	IP65, IP66K, IP67 (EN 60529)
Locking	,
	PUR
( -Ø)	10 mm
	DIN EN 61076-2-101 (M12)
	3
	-25...+85 °C ( )
EAN	4048879171748
eClass	27279218
	85444290
	DE
	1