





7/8" female 0° with cable

PUR 5x1.0 gy 7m

Female straight  
7/8" (5-pole)  
Power cable  
with cable sleeves  
Further cable lengths on request.  
Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



|                   |        |
|-------------------|--------|
| Cable length      | 7 m    |
| Side 1            |        |
| Tightening torque | 1,5 Nm |

|                                          |                                                                                                    |
|------------------------------------------|----------------------------------------------------------------------------------------------------|
| Thread                                   | 7/8"                                                                                               |
| 제품자료                                     |                                                                                                    |
| ECLASS-6.0                               | 27279218                                                                                           |
| ECLASS-6.1                               | 27279218                                                                                           |
| ECLASS-7.0                               | 27279218                                                                                           |
| ECLASS-8.0                               | 27279218                                                                                           |
| ECLASS-9.0                               | 27060327                                                                                           |
| ECLASS-10.1                              | 27060311                                                                                           |
| ECLASS-11.1                              | 27060311                                                                                           |
| ECLASS-12.0                              | 27060327                                                                                           |
| ETIM-5.0                                 | EC001855                                                                                           |
| GTIN                                     | 4048879403276                                                                                      |
| 세번부호                                     | 85444290                                                                                           |
| 포장단위                                     | 1                                                                                                  |
| Electrical data   Supply                 |                                                                                                    |
| Current operating per contact max.       | 12 A                                                                                               |
| Current phase - neutral                  | 230 V                                                                                              |
| Current phase - phase                    | 400 V                                                                                              |
| Device protection   Electrical           |                                                                                                    |
| Degree of protection (EN IEC 60529)      | IP67                                                                                               |
| Additional condition protection degree   | inserted, screwed                                                                                  |
| Mechanical data   Material data          |                                                                                                    |
| Coating locking                          | Nickeled                                                                                           |
| Locking material                         | Zinc die-casting                                                                                   |
| Mechanical data   Mounting data          |                                                                                                    |
| Mounting method                          | inserted, screwed, Shaking protection                                                              |
| Environmental characteristics   Climatic |                                                                                                    |
| Operating temperature min.               | -25 °C                                                                                             |
| Operating temperature max.               | 85 °C                                                                                              |
| Additional condition temperature range   | depending on cable quality                                                                         |
| Installation   Cable                     |                                                                                                    |
| Cable identification                     | 965                                                                                                |
| Printing color of wire insulation        | black (white isolation), white (isolation black), black (isolation brown), black (insulation blue) |
| Jacket Color                             | gray                                                                                               |
| Amount stranding                         | 1                                                                                                  |
| Stranding                                | 5 wires around Filler twisted                                                                      |
| Filler                                   | yes                                                                                                |
| wire arrangement                         | white 4, brown 3, green-yellow, blue 2, black 1                                                    |
| Cable weigth                             | 86,9 g/m                                                                                           |
| Material jacket                          | PUR                                                                                                |
| Shore hardness jacket                    | 90 ± 5 Shore A                                                                                     |
| Freedom from ingredients (jacket)        | lead-free, cadmium-free, CFC-free, silicone-free                                                   |
| Outer-diameter (jacket)                  | 7,2 mm                                                                                             |
| Tolerance outer diameter (sheath)        | ± 5 %                                                                                              |
| Material inner jacket                    | PVC                                                                                                |
| Color (inner jacket)                     | gray                                                                                               |
| Material wire insulation                 | PP                                                                                                 |
| Amount wires                             | 5                                                                                                  |
| Outer diameter insulation                | 2 mm                                                                                               |
| Outer diameter tolerance core insulation | ± 5 %                                                                                              |
| Shore hardness wire insulation           | 60 ± 5 Shore D                                                                                     |

|                                                   |                                                                                                    |
|---------------------------------------------------|----------------------------------------------------------------------------------------------------|
| Ingredient freeness wire insulation               | lead-free, CFC-free, halogen-free                                                                  |
| Printing color of wire insulation                 | black (white isolation), white (isolation black), black (isolation brown), black (insulation blue) |
| Amount strands (wire)                             | 28                                                                                                 |
| Diameter of single wires                          | 0,205 mm                                                                                           |
| Conductor crosssection (wire)                     | 1 mm²                                                                                              |
| Material conductor wire                           | Stranded copper wire, bare                                                                         |
| Conductor type (wire)                             | Strand class 5                                                                                     |
| Nominal voltage AC max.                           | 600 V                                                                                              |
| Current load capacity (standard)                  | to DIN VDE 0298-4                                                                                  |
| Current load capacity min. wire                   | 11,3 A                                                                                             |
| Electrical resistance line constant wire          | 19,5 Ω/km @ 20 °C                                                                                  |
| AC withstand voltage (wire - wire)                | 3 kV @ 60 s                                                                                        |
| Power frequency withstand voltage (wire - jacket) | 3 kV @ 60 s                                                                                        |
| Min. operating temperature (static)               | -30 °C                                                                                             |
| Max. operating temperature (fixed)                | 70 °C                                                                                              |
| Operating temperature min. (dynamic)              | -5 °C                                                                                              |
| Operating temperature max. (dynamic)              | 70 °C                                                                                              |
| Flame resistance                                  | IEC 60332-2-2   UL 1581 § 1100 FT2   UL 1581 § 1090                                                |
| chemical resistance                               | Good, application-related testing                                                                  |
| Gasoline resistance                               | Good, application-related testing                                                                  |
| Oil resistance                                    | Good, application-related testing   DIN EN 60811-404                                               |
| Bending radius (fixed)                            | 7,5 x Outer diameter                                                                               |
| Bending radius (dynamic)                          | 10 x Outer diameter                                                                                |