


7/8" female 90° screw terminal

5-pol., max. 2,5mm², 8 - 10mm


Female 90°
7/8" (5-pole)
Sealing range (cable Ø): 8...10 mm
Screw terminals
Plastic housings with good resistance against chemicals and oils.
The resistance to aggressive media should be individually tested for your application. Further details on request.

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.



Side 1	
Tightening torque	1,5 Nm
Mounting method	inserted, screwed
Family construction form	7/8"
Thread	7/8"

Gender	female
Cable outlet	angled
No. of poles	5
Side 2	
Mounting method	field-wireable
제품자료	
ECLASS-6.0	27279218
ECLASS-6.1	27260702
ECLASS-7.0	27440102
ECLASS-8.0	27440102
ECLASS-9.0	27440116
ECLASS-10.1	27440102
ECLASS-11.1	27440102
ECLASS-12.0	27440116
ETIM-5.0	EC002635
GTIN	4048879631709
세번부호	85366990
포장단위	1
Electrical data Supply	
Operating voltage AC max.	300 V
Operating voltage DC max.	300 V
Current operating per contact max.	9 A
Diagnostics	
Status indication LED	no
Installation	
Connection cross section max.	2,5 mm²
Device protection	
Shielded	no
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP67
Additional condition protection degree	inserted, screwed
Mechanical data Material data	
Material gasket	FKM
Material housing	PBT
Mechanical data Mounting data	
Mounting method	inserted, screwed, Shaking protection
Clamping range min.	8 mm
Clamping range max.	10 mm
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	85 °C
Important installation notes	
Note on strain relief	Protect the connectors by suitable measures from mechanical loads, e.g. by the usage of cable ties.
Note on bending radius	Attention: Observe the permissible bending radii when laying cables, as the IP protection class can be endangered by excessive bending forces.