

M8 panel feed through male / female 0° A-cod.

4-pol., shielded

Control cabinet entry system

Male - female




M8, 4-pole


Rear mounting

shielded

제품 링크

일러스트





실제 제품은 이미지와 다를 수 있습니다.

Side 1	
Family construction form	M8
Material contact	Copper alloy
No. of poles	4
제품자료	
ECLASS-6.0	27143423
ECLASS-7.0	27449001
ECLASS-8.0	27449001
ECLASS-9.0	27440321
ECLASS-10.1	27440109
ECLASS-11.1	27440109
ECLASS-12.0	27440109
ETIM-5.0	EC002640
GTIN	4048879689304
세번부호	85366990
포장단위	1
Electrical data Supply	
Operating voltage DC	60 V
Current operating per contact max.	4 A
Diagnostics	
Status indication LED	no
Installation Connection	
Mating cycles min.	100
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP67
Additional condition protection degree	inserted, screwed
Pollution Degree	3
Rated surge voltage	1,5 kV
Overvoltage category (EN 60950-1)	II
Mechanical data	
Contour for corrugated hose	without
Mechanical data Material data	
Coating contact	gold plated
Material housing	Metal
Material contact carrier	PA

Mounting method	inserted, screwed
-----------------	-------------------

Operating temperature min.	-25 °C
Operating temperature max.	85 °C