

COVER PUSH PULL POWER

Push Pull Power
Protective cover

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.

제품자료

ECLASS-6.0	23111190
ECLASS-7.0	23111190
ECLASS-8.0	23111190
ECLASS-9.0	23111190
ECLASS-10.1	27440192
ECLASS-11.1	27440192
ECLASS-12.0	27440192
ETIM-5.0	EC002635
GTIN	4048879113519
세번부호	85389099
포장단위	1

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65, IP67
Additional condition protection degree	inserted, screwed

Mechanical data | Material data

Coating housing	nickel plated
Material housing	Zinc die-casting

Environmental characteristics | Climatic

Operating temperature min.	-40 °C
Operating temperature max.	85 °C