

**M12 FEMALE 0° V2A**

PUR 5X0.34 YELLOW, UL/CSA, drag ch 10m



Female

M12, 5

Art-No. 7005 -M12 Lite ( , ) .



1.4305 (V2A)

stay connected



(\* for cable type 126, 732, 219, 619)

## Female



\* UL/CSA

12241

5x 0.34 mm<sup>2</sup>

	PP ( , , , / )
C-track	10 Mio.
	PUR (UL/CSA)
	4.8 mm ±5%
( )	10× Ø
( )	-40...+80 °C
( )	-25...+80 °C
	035
	3 (PUR)
( )	cRUus (AWM-Style 20549/10493); CE conform
[G/m]	41,80
(wire)	,
( )	max. 57 Ω/km (20 °C)
-Ø	0.1 mm
( )	42× 0.1 mm (6 )
( )	5× 0.34 mm <sup>2</sup>
AWG	AWG 22
( )	PP
( )	CFC, , , , ,
( )	70 ±5 D
-Ø	1.25 mm ±5%
/	, , , , / ( )
	5 .
(shielded)	no
	PUR
( )	CFC, , , , , , , , , ,
( )	90 ±5 A
-Ø ( )	4.8 mm ±5%
( )	, , (EN 60811-404)
	300 V AC
	2500 V AC
	DIN VDE 0298-4
( )	-40...+80 °C, (+90 °C 10 000 )
( )	-25...+80 °C, (+90 °C 10 000 )
( )	5× Ø
( )	10× Ø
(C-track)	max. 10 Mio. (25 °C)
(C-track)	max. 3 m/s
(C-track)	max. 10 m/s <sup>2</sup>
	±180°/m
	max. 2 Mio. (25 °C)
	35
	max. 125 V AC/DC
(UL )	max. 30 V AC/DC
	max. 4 A
	IEC 60664-1, category I

	A-coded
	(M12×1 mm) 0.6 Nm ,
	M12 (SW13)
	IP66K, IP67 (EN 60529)
Locking	1.4305 (V2A)
	PUR
( -Ø)	10 mm
	DIN EN 61076-2-101 (M12)
	3
	-25...+85 °C ( )
EAN	4048879372718
eClass	27279218
	85444290
	DE
	1