

1,6 mm crimp contact f/turned/silver/0,14-0,37 mm²

100 pieces

Turned crimp contact
Female
1.6 mm
0.14...0.37 mm² (AWG 26...22)
Quantity: 100 pcs.
Technical data will be only guaranteed with Murrelektronik components.

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.

제품자료	
ECLASS-6.0	27143424
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
GTIN	4048879653503
세번부호	85366990
포장단위	100
Installation	
Connection cross section min.	0,14 mm²
Connection cross section max.	0,37 mm²
AWG number min.	26
AWG number max.	22
Installation Connection	
Stripping length	7 mm
Connection	Crimp
Gender	female
Mating cycles min.	500
Mechanical data Material data	

Coating contact	silver-plated
Material contact	Brass
Mechanical data Mounting data	
Height	3,5 mm
Width	3,5 mm
Depth	21,6 mm