

GigaBit crimp contact - F, 0,2-0,5 mm²

GigaBit crimp contact - F, 0,2-0,5 mm²
Turned crimp contact
Female
Technical data will be only guaranteed with Murrelektronik components.

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.

제품자료	
ECLASS-6.0	27261204
ECLASS-6.1	27261202
ECLASS-7.0	27440204
ECLASS-8.0	27440204
ECLASS-9.0	27440204
ECLASS-10.1	27440204
ECLASS-11.1	27440204
ECLASS-12.0	27440204
ETIM-5.0	EC000796
GTIN	4048879672863
세번부호	85366990
포장단위	100
Installation	
Connection cross section min.	0,2 mm²
Connection cross section max.	0,5 mm²
AWG number min.	24
AWG number max.	20
Installation Connection	
Stripping length	4,2 mm
Connection	Crimp
Gender	female
Mating cycles min.	200
Mechanical data Material data	
Coating contact	gold plated
Material contact	Copper alloy
Mechanical data Mounting data	

Height	1,7 mm
Width	1,7 mm
Depth	13,6 mm