

Pneumatic insert - male, 3 mm

Pneumatic male
Internal hose Ø
3 mm
Technical data will be only guaranteed with Murrelektronik components.

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.

제품자료	
ECLASS-6.0	27261204
ECLASS-6.1	27261290
ECLASS-7.0	27440290
ECLASS-8.0	27440290
ECLASS-9.0	27440220
ECLASS-10.1	27440220
ECLASS-11.1	27440220
ECLASS-12.0	27440220
ETIM-5.0	EC000438
GTIN	4048879672757
세번부호	39269097
포장단위	10
Installation Connection	
Gender	male
Mating cycles min.	500
Mechanical data	
Operating pressure max.	8 bar
Integrated valve	no
Mechanical data Material data	
Material housing	Delrin Acetal
Mechanical data Mounting data	
Internal hose Ø	3 mm
Environmental characteristics Climatic	
Operating temperature min.	-40 °C
Operating temperature max.	80 °C

