

MODL. VARIO 6-way fixed housing type B

nickel plated aluminum

Stationary housing (round)
Aluminium
6-way

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.

제품자료	
ECLASS-6.0	27260702
ECLASS-6.1	27260708
ECLASS-7.0	27440312
ECLASS-8.0	27440312
ECLASS-9.0	27440312
ECLASS-10.1	27440312
ECLASS-11.1	27440312
ECLASS-12.0	27440312
ETIM-5.0	EC002641
GTIN	4048879572996
세번부호	85389099
포장단위	1
Device protection Electrical	
Degree of protection (EN IEC 60529)	IP65, IP67, IP68
Degree of protection (ISO 20653:2013)	IP66K, IP69K
Additional condition protection degree	inserted, screwed
Mechanical data	
Operating pressure min.	-0,8 bar
Operating pressure max.	16 bar
Mechanical data Material data	
Coating housing	powder-coated
Material housing	Aluminum die casting
Mechanical data Mounting data	
Mounting method	screw fixing
Environmental characteristics Climatic	

이 데이터 시트에 포함된 정보는 최대한의 주의로 작성되었습니다.
2024-04-25

Operating temperature min.	-20 °C
Operating temperature max.	120 °C