

MODL. VARIO 6-way coupling housing type B

nickel plated aluminum

Mobile housing (round)
Aluminium
6-way

제품 링크

일러스트



실제 제품은 이미지와 다를 수 있습니다.

제품자료	
ECLASS-6.0	27260702
ECLASS-6.1	27260708
ECLASS-7.0	27440312
ECLASS-8.0	27440312
ECLASS-9.0	27440312
ECLASS-10.1	27440312
ECLASS-11.1	27440312
ECLASS-12.0	27440312
ETIM-5.0	EC002641
GTIN	4048879573009
세번부호	85389099
포장단위	1
Mechanical data	
Operating pressure min.	-0,8 bar
Operating pressure max.	16 bar
Mechanical data Material data	
Coating housing	nickel plated
Material housing	Aluminium
Mechanical data Mounting data	
Looking techniques	Clip locking
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	120 °C