



AMS 4-10/44-2 OPTO-COUPLER MODULE

In: 24 VDC - Out: 24 VDC / 2A

Transistor 2 A (4-way)
4 NO contacts
24 V DC

Ürün Linki

örnekleme



Ürün Image farklı olabilir



Ticari bilgiler

ECLASS-6.0	27371604
ECLASS-6.1	27371604
ECLASS-7.0	27371604
ECLASS-8.0	27371604
ECLASS-9.0	27371604
ECLASS-10.1	27371604

ECLASS-11.1	27371604
ECLASS-12.0	27371604
ETIM-5.0	EC001504
GTIN	4048879295451
Gümrük tarife no (gtip)	85414900
Paket miktarı	1
Electrical data Input	
Input voltage OFF DC min.	0 V
Input voltage OFF DC max.	6 V
Input voltage DC min.	20 V
Input voltage DC max.	30 V
Input current	27 mA
Electrical data Output	
Switch off delay max.	5 ms
Switch on delay max.	1 ms
Quiescent current OFF max.	0,01 mA
Switching frequency inductive max.	1 Hz
Switching frequency ohmic max.	10 Hz
Voltage switching DC min.	5 V
Switching voltage DC max.	30 V
Switching current min.	1 mA
Switching current max.	2 A
Voltage drop DC max.	0,05 V
Diagnostics	
Status indication LED	yellow
Device protection Electrical	
Rated surge voltage	2,5 kV
Device protection Media	
Flame resistance	flame retardant
Mechanical data Material data	
Color housing	black
Material housing	Plastic
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, G32, (EN 60715)
Height	75 mm
Width	22,5 mm
Depth	102 mm
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	50 °C