

PROFIBUS-PLUG-MALE (SUB-D) 90°

Screw terminals up to 12Mbps/s

Bus connection plug 90°
SUB-D9 (male), screw terminals
PROFIBUS

Ürün Linki

örnekleme



Ürün Image farklı olabilir

Ticari bilgiler

ECLASS-6.0	27279221
ECLASS-7.0	27440104
ECLASS-8.0	27440104
ECLASS-9.0	27440102
ECLASS-10.1	27242692
ECLASS-11.1	27242692
ECLASS-12.0	27242692
ETIM-5.0	EC002584
GTIN	4048879049818
Gümrük tarife no (gtip)	85366990
Paket miktarı	1

Electrical data

Terminating resistor	connectable, integrated
----------------------	-------------------------

Electrical data | Supply

Operating voltage DC min.	4,75 V
Operating voltage DC max.	5,25 V
Current consumption max.	12,5 mA

Industrial communication

Data transmission rate max.	12 MBit/s
-----------------------------	-----------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP20
-------------------------------------	------

Mechanical data | Mounting data

Height	64 mm
Width	40 mm
Depth	17 mm

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	60 °C
Storage temperature min.	-25 °C
Storage temperature max.	80 °C