

POTENTIAL TERMINAL BLOCK BL.YELL.BR.BL

Potential terminal block
blue/yellow/brown/blue

Ürün Linki**örnekleme**

Ürün Image farklı olabilir

	00	01	02	03	04	05	06	07	08	09
X0										
X1										
X2										
X3										

**Ticari bilgiler**

ECLASS-6.0	27141106
ECLASS-6.1	27141106
ECLASS-7.0	27141106
ECLASS-8.0	27141106
ECLASS-9.0	27141106
ECLASS-10.1	27141106
ECLASS-11.1	27141106
ECLASS-12.0	27141106
ETIM-5.0	EC001283
GTIN	4048879049351
Gümrük tarife no (gtip)	85369010
Paket miktarı	1

Electrical data | Supply

Operating voltage AC max.	30 V
Operating voltage DC max.	30 V
Total current max.	10 A

Installation

Connection cross section max.	2,5 mm ²
AWG number min.	28
AWG number max.	14

Installation | Connection

Connection	Spring clamp plug-in terminals
------------	--------------------------------

Device protection | Electrical

Degree of protection (EN IEC 60529) IP20

Mechanical data | Mounting data

Height	70 mm
Width	56 mm
Depth	32,5 mm

Environmental characteristics | Climatic

Operating temperature min.	0 °C
Operating temperature max.	55 °C
Storage temperature min.	-40 °C
Storage temperature max.	85 °C