

MCS-B POWER SUPPLY 1-PHASE,

IN: 95-265VAC OUT: 24V/2,5ADC



INPUT: 95...265 V AC

OUTPUT: 24 V DC +3/-1%

Current: 2.5 A

Mains failure bridging min.

min. 15 ms (110 V AC); min. 80 ms (230 V AC)

Ürün Linki**örnekleme**

Ürün Image farklı olabilir

**Ticari bilgiler**

ECLASS-6.0	27049002
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-8.0	27049002
ECLASS-9.0	27040701

ECLASS-10.1	27040701
ECLASS-11.1	27040701
ECLASS-12.0	27040701
ETIM-5.0	EC002540
GTIN	4048879000116
Gümrük tarife no (gtip)	85044095
Paket miktarı	1

Electrical data

Number of devices parallel connection max.	5
Number of devices series connection max.	2
Parallel connection	yes
Series connection	yes
Security level	SELV

Electrical data | Supply

Power frequency	50 ... 60 Hz
-----------------	--------------

Electrical data | Input

Input voltage 1 AC	110 V
Input voltage 2 AC	230 V
Input voltage AC min.	95 V
Input voltage AC max.	265 V
Input voltage DC min.	110 V
Input voltage DC max.	300 V
Input current at input voltage 1 AC	1,04 A
Input current at input voltage 2 AC	0,63 A
Inrush current max.	20 A
External back-up fuse per phase max.	10 A
Efficiency	85 % @ 110 V AC, 87 % @ 230 V AC

Electrical data | Output

Output voltage DC	24 V
Output voltage DC min.	22 V
Output voltage DC max.	28 V
Output voltage adjustable	yes
Output current	2,5 A
Ripple effective max.	50 mV
Spikes (s-s) max.	120 mV

Device protection | Electrical

Overload protection output	yes
Short-circuit protection output	yes

Mechanical data | Mounting data

Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)
Height	76 mm
Width	38 mm
Depth	108 mm

Environmental characteristics | Climatic

Operating temperature min.	-25 °C
Operating temperature max.	40 °C
Derating from	40 °C
Storage temperature min.	-25 °C
Storage temperature max.	85 °C
Relative humidity min. (operation)	5 %

Relative humidity max. (operation) 95 % no condensation

Connection type 2

Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	2
PIN 1	-
PIN 2	+
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	3
PIN 1	PE
PIN 2	N
PIN 3	L