

Emparro Cap 40/24 300ms



INPUT: 24 V DC (SELV/PELV)

OUTPUT: max. 40 A

min. 0.3 s (40 A); min. 1.2 s (10 A); min. 2.4 s (5 A); min. 8 s (1.5 A)

Ürün Linki

örnekleme



Ürün Image farklı olabilir



Ticari bilgiler

ECLASS-6.0	27049190
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-8.0	27049002
ECLASS-9.0	27040705
ECLASS-10.1	27040705
ECLASS-11.1	27040705
ECLASS-12.0	27040705

ETIM-5.0	EC002584
GTIN	4048879790956
Gümrük tarife no (gtip)	85044095
Paket miktarı	1
Electrical data	
Parallel connection	yes
Security level	SELV/PELV
Electrical data Input	
Input voltage DC min.	22 V
Input voltage DC max.	28 V
Charging current max.	1 A
Charging time min.	22 s
Charging time max.	65 s
Protection against voltage peaks DC max.	36 V
Efficiency	99 %
Electrical data Output	
Output voltage DC	22,5 V
Output voltage DC min.	21 V
Output voltage DC max.	27 V
Output voltage adjustable	yes
Output current buffer operation	48 A
Output current max.	40 A
Ripple (s-s) max.	500 mV
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)
Height	123 mm
Width	66,5 mm
Depth	167 mm
Environmental characteristics Climatic	
Operating temperature min.	-25 °C
Operating temperature max.	70 °C
Storage temperature min.	-40 °C
Storage temperature max.	85 °C
Conformity	
EMC	EN 55022 B
Connection type 2	
Connection type 1	Input / Output
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green
No. of poles	4
PIN 1	- In DC
PIN 2	+ In DC
PIN 3	- Out
PIN 4	+ Out
Connection	Spring clamp terminals FK
Family construction form	terminal
Gender	female
Color contact carrier	green

No. of poles	4
PIN 1	+
PIN 2	A
PIN 3	R
PIN 4	I