

MB CAP ULTRA BUFFER MODULE

IN: 24VDC OUT: 24VDC/20A for max. 1A/320S



INPUT: 24 V DC (SELV/PELV)

OUTPUT: max. 20 A

16 s (20 A); 320 s (1 A)

Ürün Linki

örnekleme



Ürün Image farklı olabilir



Ticari bilgiler

ECLASS-6.0	27049190
ECLASS-6.1	27049002
ECLASS-7.0	27049002
ECLASS-8.0	27049002
ECLASS-9.0	27040705
ECLASS-10.1	27040705

ECLASS-11.1	27040705
ECLASS-12.0	27040705
ETIM-5.0	EC002584
GTIN	4048879079778
Gümrük tarife no (gtip)	85322900
Paket miktarı	1
Electrical data Input	
Max. inrush current duration	2 ms
Input voltage DC min.	24 V
Input voltage DC max.	29 V
Current input AC	20 A
Max. inrush current	36,5 A
Charging time min.	40 s
Charging time max.	500 s
Efficiency	90 %
Electrical data Output	
Output voltage DC	23,3 V
Output voltage DC min.	22,83 V
Output voltage DC max.	23,77 V
Output voltage adjustable	no
Output current	20 A
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	Tragschiene TH35-7.5/TH35-15, (EN 60715)
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Derating from	60 °C
Storage temperature min.	-20 °C
Storage temperature max.	60 °C
Conformity	
Product standard	IEC 61010-2-201
EMC	EN 55011 A
Low Voltage Directive	EN 61204-3