



NG 5 RECTIFIER UNIT 1-PHASE

IN: 41VAC OUT: 24V/5A

Rectifiers, single phase
 INPUT: max. 41 V AC
 Output rating: 120 W
 Current: max. 5 A

Ürün Linki

örnekleme



Ürün Image farklı olabilir



Ticari bilgiler

ECLASS-6.0	27049002
ECLASS-6.1	27040390
ECLASS-7.0	27040390
ECLASS-8.0	27040390
ECLASS-9.0	27040390
ECLASS-10.1	27040390

ECLASS-11.1	27040390
ECLASS-12.0	27040390
ETIM-5.0	EC002540
GTIN	4048879079488
Gümrük tarife no (gtip)	85044083
Paket miktarı	1
Electrical data Supply	
Power frequency	45 ... 65 Hz
Electrical data Input	
Fuse protection primary side internal	8 A
Type of primary fuse	Microfuse 5 × 20 mm
Characteristic back-up fuse	Inertia
Input voltage AC min.	5 V
Input voltage AC max.	44 V
Input current DC max.	5 A
Electrical data Output	
Output suppression	LED, screened with electrolytic capacitor
Output voltage DC max.	60 V
Output voltage adjustable	no
Output current max.	5 A
Ripple max.	5 %
Mechanical data Mounting data	
Mounting method	geschnappt
Suitable for mounting type	Mounting rail TH35, (EN 60715)
Height	90 mm
Width	68 mm
Depth	87 mm
Environmental characteristics Climatic	
Operating temperature min.	-20 °C
Operating temperature max.	60 °C
Derating from	20 °C
Connection type 2	
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	2
PIN 1	U E AC
PIN 2	U E AC
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	4
PIN 1	U A -
PIN 2	U A -
PIN 3	U A +
PIN 4	U A +