



MTL 1-PHASE SAFETY TRANSFORMER

P: 250VA IN: 230/400VAC +/- 15VAC OUT: 2x24VAC


The MTL series comprises single-phase safety transformers/isolating transformers of the protection class I and protection degree IP20 with double insulation between the primary and secondary windings for general use in industrial applications.

Ürün Linki

örnekleme



Ürün Image farklı olabilir



Ticari bilgiler

ECLASS-6.0	27031302
ECLASS-7.0	27031302
ECLASS-8.0	27031302
ECLASS-9.0	27031302
ETIM-5.0	EC002486
GTIN	4048879078306
Gümrük tarife no (gtip)	85043180

Paket miktarı 1

Electrical data | Supply

Power frequency 50 ... 60 Hz

Electrical data | Input

Input voltage 1 AC 230 V

Input voltage 1 AC min. 195,5 V

Input voltage 1 AC max. 264,5 V

Input voltage 2 AC 400 V

Input voltage 2 AC min. 340 V

Input voltage 2 AC max. 460 V

Input current at input voltage 1 AC 1,29 A

Input current at input voltage 2 AC 0,75 A

Inrush current at input voltage 1 14,1 A

Inrush current at input voltage 2 8,15 A

Short-circuit current at input voltage 1 27,5 A

Short-circuit current at input voltage 2 15,9 A

Electrical data | Output

Output voltage 1 × 24 / 1 × 48 / 2 × 24 V AC

Output voltage AC 1 48 V

Output voltage AC 2 24 V

Output voltage adjustable yes

Power rating AC max. 250 VA

Diagnostics

Status indication LED green

Device protection | Electrical

Insulation test voltage input - output 5,1 kV

Mechanical data | Mounting data

Suitable for mounting type Schlüssellochabhängung

Mounting dimension a 136 mm

Mounting dimension b 82 mm

Mounting dimension c 6,5 mm

Height 153 mm

Width 123 mm

Depth 142 mm

Diameter bore 6,5 mm

Length bore 11 mm

Environmental characteristics | Climatic

Operating temperature min. -20 °C

Operating temperature max. 60 °C

Conformity

Product standard EN 61558-2-4, EN 61558-2-6, EN 62041 category 0

Connection type 2

Connection type 1 Input

Connection type 2 Output

Connection Screw terminals SK

Family construction form terminal

Gender female

No. of poles 5

PIN 1 + 15 V

PIN 3 - 15 V

PIN 4 230 V

PIN 5	400 V
Connection	Screw terminals SK
Family construction form	terminal
Gender	female
No. of poles	5
PIN 1	PE
PIN 2	1
PIN 3	2
PIN 4	3
PIN 5	4