

MODLINK MSDD SOCKET INSERT GERMANY

250VAC/16A, spring clamp connection

Germany (VDE) white
Spring clamp terminals**Ürün Linki**

örnekleme



Ürün Image farklı olabilir

**Ticari bilgiler**

ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC000020
GTIN	4048879038140
Gümrük tarife no (gtip)	85366990
Paket miktarı	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	33 mm

Environmental characteristics | Climatic

Storage temperature min.	-25 °C
Storage temperature max.	40 °C

Germany (VDE)

Connection cross section max.	2,5 mm ²
AWG number max.	14

Operating voltage AC	230 V
Operating current	16 A
Connection	Spring clamp terminals FK
No. of poles	2 + PE
Connections per pole	2
Protection contact present	yes