

MODLINK MSDD DATA INSERT

1xUSB-A female/female + 1xRJ45

USB (form A); RJ45

1x USB 3.0 (female/female) form A

1x RJ45, 8-pole metal, CAT5e (female/female)

Ürün Linki

örnekleme



Ürün Image farklı olabilir

**Ticari bilgiler**

ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27189217
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC002625
GTIN	4048879037587
Gümrük tarife no (gtip)	85366990
Paket miktarı	1

Mechanical data | Mounting data

Height	88 mm
Width	51 mm
Depth	70,4 mm

Environmental characteristics | Climatic

Storage temperature min.	5 °C
Storage temperature max.	40 °C

Shielding plate

Connection information	Threaded hole M4
------------------------	------------------

Tightening torque 0,9 Nm

USB

Operating voltage AC	48 V
Operating voltage DC	48 V
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Operating current	1,5 A
USB specification	3.0
Data transmission rate max.	5000 MBit/s
Looking techniques	Snap-in connector

RJ45

Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA
Family construction form	RJ45
Family type Back side	RJ45
Cable category min.	Cat5e
Looking techniques	Snap-in connector