

MODLINK MSDD SINGLE COMBI INSERT GERMANY

1x RJ45 + 1x data cutout

1x Germany (VDE) white

1x RJ45, 8-pole metal, CAT6A (female/female)

1x RJ45 cut-out

Ürün Linki

örnekleme



Ürün Image farklı olabilir

**Ticari bilgiler**

ECLASS-6.0	27189217
ECLASS-6.1	27189217
ECLASS-7.0	27189217
ECLASS-8.0	27189217
ECLASS-9.0	27182806
ECLASS-10.1	27182806
ECLASS-11.1	27182806
ECLASS-12.0	27182806
ETIM-5.0	EC002625
GTIN	4048879600880
Gümrük tarife no (gtip)	85366990
Paket miktarı	1

Device protection | Electrical

Degree of protection (EN IEC 60529) IP20

Mechanical data | Mounting data

Height	87,5 mm
Width	50,7 mm
Depth	43 mm

Environmental characteristics | Climatic

Operating temperature min.	-5 °C
Operating temperature max.	50 °C

Storage temperature min.	-10 °C
Storage temperature max.	60 °C
Shielding plate	
Connection information	Threaded hole M4
Tightening torque	0,9 Nm
Germany (VDE)	
Connection cross section max.	2,5 mm ²
AWG number max.	14
Operating voltage AC	250 V
Operating current	16 A
Connection	Spring clamp terminals FK
No. of poles	2 + PE
Connections per pole	2
Protection contact present	yes
RJ45	
Operating voltage AC max. (UL-listed)	30 V
Operating voltage DC max. (UL-listed)	42,4 V
Current operating max. (UL)	175 mA
Family construction form	RJ45
Family type Back side	RJ45
Cable category min.	Cat6a
Looking techniques	Snap-in connector