


**Modlink MSDD-set: Frame 4000-68122-0000000,**  
insert 4000-68000-1210000 + 4000-68000-0010000

### Ürün Linki

örnekleme



Ürün Image farklı olabilir

**Ticari bilgiler**

|                         |               |
|-------------------------|---------------|
| ECLASS-6.0              | 27189217      |
| ECLASS-6.1              | 27189217      |
| ECLASS-7.0              | 27189217      |
| ECLASS-8.0              | 27189217      |
| ECLASS-9.0              | 27189217      |
| ECLASS-10.1             | 27182806      |
| ECLASS-11.1             | 27182806      |
| ECLASS-12.0             | 27182806      |
| ETIM-5.0                | EC002625      |
| GTIN                    | 4048879035408 |
| Gümrük tarife no (gtip) | 85366990      |
| Paket miktarı           | 1             |

**Frame**

|                                               |                       |
|-----------------------------------------------|-----------------------|
| Degree of protection (EN IEC 60529)           | IP65                  |
| Operating temperature min.                    | -10 °C                |
| Operating temperature max.                    | 60 °C                 |
| Storage temperature min.                      | -25 °C                |
| Storage temperature max.                      | 60 °C                 |
| Suitable for installation wall thickness min. | 1 mm                  |
| Suitable for installation wall thickness max. | 5 mm                  |
| Coating housing                               | KTL                   |
| Material housing                              | Fine zinc die casting |

**Germany (VDE)**

|                               |                    |
|-------------------------------|--------------------|
| Connection cross section max. | 6 mm <sup>2</sup>  |
| AWG number max.               | 10                 |
| Operating voltage AC          | 250 V              |
| Operating current             | 16 A               |
| Status indication LED         | yellow             |
| Connection                    | Screw terminals SK |
| No. of poles                  | 2 + PE             |
| Connections per pole          | 2                  |
| Protection contact present    | yes                |

**RJ45**

|                                       |                   |
|---------------------------------------|-------------------|
| Operating voltage AC max. (UL-listed) | 30 V              |
| Operating voltage DC max. (UL-listed) | 42,4 V            |
| Current operating max. (UL)           | 175 mA            |
| Family construction form              | RJ45              |
| Family type Back side                 | RJ45              |
| Cable category min.                   | Cat5e             |
| Looking techniques                    | Snap-in connector |