

COMLIGHT57 LED GREEN STATUS LIGHT

Product discontinued

Compact status light
Flange M12 male, 4-pole
green

Ürün Linki

örnekleme



Ürün Image farklı olabilir

**Ticari bilgiler**

ECLASS-6.0	27371220
ECLASS-7.0	27371220
ECLASS-8.0	27371220
ECLASS-9.0	27371220
ETIM-5.0	EC000232
GTIN	4048879440141
Gümrük tarife no (gtip)	85318070
Paket miktarı	1

Electrical data | Supply

Operating voltage DC	24 V
Current consumption max.	23 mA

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked

Mechanical data | Material data

Material housing	Plastic
------------------	---------

Mechanical data | Mounting data

Height	78,4 mm
Width	57 mm
Depth	57 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	50 °C

Connection type 1

Family construction form	M12
Gender	male
Coding	A
No. of poles	4
PIN 3	BU 0 V
PIN 4	BK 24 V DC