

MODLIGHT50/70 MAGNET BASE WITH M12 8-POLE

Side cable entry

Magnet base
with M12 flange plug connector (8-pole)**Ürün Linki**

örnekleme



Ürün Image farklı olabilir

Ticari bilgiler

ECLASS-6.0	27371235
ECLASS-6.1	27371235
ECLASS-7.0	27371235
ECLASS-8.0	27371235
ECLASS-9.0	27371235
ECLASS-10.1	27371235
ECLASS-11.1	27371235
ECLASS-12.0	27371235
ETIM-5.0	EC001154
GTIN	4048879031080
Gümrük tarife no (gtip)	85319000
Paket miktarı	1

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
-------------------------------------	------

Mechanical data | Material data

Color housing	black
Material housing	Aluminium

Mechanical data | Mounting data

Height	35 mm
Width	70 mm
Depth	70 mm

Connection type 2

Family construction form	M12
Gender	male
Coding	A
No. of poles	5

PIN 1	n.c.
PIN 2	n.c.
PIN 3	0 V DC
PIN 4	24 V DC
PIN 5	FE
Family construction form	M12
Gender	male
Coding	A
No. of poles	8