



Modlight Illumix Slim Line 16W



RGBW-LED machine lamp, IP54, 24VDC, M12 connection

Modlight Illumix Slim Line
16 W

Ürün Linki

örnekleme





Ürün Image farklı olabilir



General product information

URI product <https://shop.murrelektronik.com/4000-75800-1416016>

Ticari bilgiler

ECLASS-6.0	27110306
ECLASS-6.1	27110390
ECLASS-7.0	27110390
ECLASS-8.0	27110390
ECLASS-9.0	27110345
ECLASS-10.1	27110345
ECLASS-11.1	27110345
ECLASS-12.0	27110345
ETIM-5.0	EC000348
GTIN	4065909086674
Gümrük tarife no (gtip)	94054239
Paket miktarı	1

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	27,6 V
Power consumption max.	17,28 W
Power consumption illumination white	16 W
Power consumption red	5,76 W
Power consumption green	5,76 W

HMI | Illumination properties

Number of light sources	3
Radiation angle min.	120 °
Luminous efficacy	135 lm/W
Light color	daylight white
Luminous temperature	5700 K
Color reproduction (Ra) min.	80
LED service life L70 min.	52000 h
Energy efficiency class (EU 2019/2015)	E

Luminous flux illumination white	2164 lm
Luminous flux red	188 lm
Luminous flux green	608 lm
Luminous flux blue	144 lm
Installation Connection	
Family construction form	M12
Gender	male
Installation Pin assignment	
Coding	A
No. of poles	5
Device protection Electrical	
Installation height max. ASL	2000 m
Degree of protection (EN IEC 60529)	IP54
Protection class (EN IEC 61140)	III
Device protection Mechanical	
Shock resistance (EN IEC 60068-2-27)	50 g, 11 ms
Vibration resistance (EN IEC 60068-2-6)	10 mm (2 ... 9 Hz), 3 g (9 ... 200 Hz)
Mechanical data Material data	
Coating housing	eloxiert
Material housing	Aluminium
Material light cover	Semi-diffuse polystyrene (PS)
Mechanical data Mounting data	
Net weight	357 g
Height	34 mm
Width	643 mm
Depth	24 mm
Screw head diameter max.	12 mm
Screw head thread max.	M5
Environmental characteristics Climatic	
Operating temperature min.	-30 °C
Operating temperature max.	50 °C
Storage temperature min.	-30 °C
Storage temperature max.	50 °C
Relative humidity min. (operation)	5 %
Relative humidity max. (operation)	95 %
Environmental product conformity	
REACH	compliant
RoHS	2011/65/EU
Conformity	
CE	2014/30/EU
UKCA	compliant
Approvals	
UL	E473165, UL2108 IFDR
ULc	E473165, CSA C22.2 No.250.0 IFDR7