

COMLIGHT56 LED RED STATUS LIGHT

With 4 pole M12 bottom exit

Compact status light
Flange M12 male, 4-pole
red

Ürün Linki

örnekleme



Ürün Image farklı olabilir

**Ticari bilgiler**

ECLASS-6.0	27371220
ECLASS-6.1	27110390
ECLASS-7.0	27110390
ECLASS-8.0	27110390
ECLASS-9.0	27110350
ECLASS-10.1	27110350
ECLASS-11.1	27110350
ECLASS-12.0	27110350
ETIM-5.0	EC000232
GTIN	4048879855709
Gümrük tarife no (gtip)	85319000
Paket miktarı	1

Electrical data | Supply

Operating voltage DC	24 V
Current consumption max.	26 mA

Industrial communication | HMI

Luminous intensity	735 mcd
--------------------	---------

Device protection | Electrical

Degree of protection (EN IEC 60529)	IP65
Additional condition protection degree	inserted, locked

Mechanical data | Material data

Material housing	Plastic
------------------	---------

Mechanical data | Mounting data

Height	78,8 mm
Width	56 mm
Depth	56 mm

Environmental characteristics | Climatic

Operating temperature min.	-30 °C
Operating temperature max.	50 °C

Connection type 1

Family construction form	M12
Gender	male
Coding	A
No. of poles	4
PIN 3	BU 0 V (24 V DC)
PIN 4	BK 24 V DC (0 V)