

Signal tower Modlight50 Pro equipped with LED modules

green,amber,red,buzzer

Basic, buzzer, flash + LED modules
green, yellow, red**Ürün Linki**

örnekleme



Ürün Image farklı olabilir

**Ticari bilgiler**

ECLASS-6.0	27371230
ECLASS-6.1	27371230
ECLASS-7.0	27371230
ECLASS-8.0	27371230
ECLASS-9.0	27371230
ECLASS-10.1	27371230
ECLASS-11.1	27371230
ECLASS-12.0	27371230
ETIM-5.0	EC001042
GTIN	4048879759656
Gümrük tarife no (gtip)	85318070
Paket miktarı	1

Electrical data | Supply

Operating voltage DC	24 V
Operating voltage DC min.	21,6 V
Operating voltage DC max.	26,4 V
Current consumption max.	385 mA

Industrial communication | HMI

Reduced sound pressure at 1 m	80 dB
Sound pressure at 1 m	90 dB

HMI | Illumination properties

Blink cycles 60 ±12 per minute

Device protection | Electrical

Degree of protection (EN IEC 60529) IP65
Additional condition protection degree inserted, locked

Mechanical data | Material data

Color housing black
Material housing Plastic

Mechanical data | Mounting data

Height 253,5 mm
Width 50 mm
Depth 50 mm

Environmental characteristics | Climatic

Operating temperature min. -30 °C
Operating temperature max. 60 °C